

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643204311](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: .635mm, 1.50mm, CMC Receptacle, 36 Circuits, Right Wire Output, Black Coding, Mat Sealed, Row 1 closed

Documents:

3D Model	Application Specification AS-98420-002-001 (PDF)
Drawing (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
3D Model (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	Packaging Specification PK-64320-001-001 (PDF)
Application Specification AS-64319-002-FR-001 (PDF)	Datasheet (PDF)
Application Specification AS-64319-002-SP-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link	63812-1100
Application Tooling Part Link	63824-1200

General

Product Family	Crimp Housings
Series	64320
Application	Automotive, Power, Wire-to-Board
Comments	* Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm ² wire) and 12.0A for 1.50mm Terminal (2.0mm ² wire) *
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	883906135065

Physical

Circuits (maximum)	36
Circuits Detail	6 x 1.5mm, 30 x 0.635mm terminals
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	36.000/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[64320](#) Series

Mates With
CMC Header [477320361](#) , [36638](#)

Use With
CMC CP Female Terminal [64322](#)
(0.635mm), [64323](#) (1.50mm) . CMC Wire
Cap [643201301](#) . Sealing Plugs [643251010](#)
, [643251023](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Continuity Test Pen Assembly	638121100
Unlocking Tool for CMC and	638241200

Electrical		CMX Receptacle Connector
Current - Maximum per Contact	12.0A, 2.5A	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Reference - Drawing Numbers		
Application Specification	AS-64319-002-001, AS-64319-002-CH-001, AS-64319-002-FR-001, AS-64319-002-SP-001, AS-98420-002-001, AS-98420-002-CH-001, AS-98420-002-FR-001, AS-98420-002-SP-001	
Packaging Specification	PK-64320-001-001	
Sales Drawing	643200003-000, SD-64320-003-001	

This document was generated on 12/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64320-4311](#)