

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643221229](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: 0.635mm CMC CP Female Terminal, Tin Plated, Selective 1.27µm Gold in Contact Area, for Square 0.6mm x 0.6mm Pins, Wire Size 0.35mm²

Documents:


3D Model	Application Specification AS-64322-001-CH-001 (PDF)
Drawing (PDF)	Application Specification AS-64322-001-FR-001 (PDF)
3D Model (PDF)	Application Specification AS-98420-001-001 (PDF)
Product Specification PS-64319-002-001 (PDF)	Application Specification AS-98420-001-CH-001 (PDF)
Product Specification PS-64326-001-001 (PDF)	Application Specification AS-98420-001-FR-001 (PDF)
Application Specification AS-64318-002-001 (PDF)	Application Specification AS-98420-001-SP-001 (PDF)
Application Specification AS-64318-002-CH-001 (PDF)	Application Specification AS-98420-002-001 (PDF)
Application Specification AS-64318-002-FR-001 (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
Application Specification AS-64318-002-SP-001 (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	Packaging Specification 313025040-000 (PDF)
Application Specification AS-64319-002-FR-001 (PDF)	Packaging Specification PK-98913-001-001 (PDF)
Application Specification AS-64319-002-SP-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-64322-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	64322
Application	Automotive, Signal, Wire-to-Board
Comments	* Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C. Current max = 6A for 0.635mm Terminal(0.75mm ² wire)
Crimp Quality Equipment	Yes
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC, CP Terminal
UPC	883906129514

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Gold
Net Weight	0.110/g
Packaging Type	Reel
Plating min - Mating	1.016µm, 3.048µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.25-1.40mm
Wire Size AWG	22, 24



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[64322](#) Series

Use With

CMC Connector [64318](#) , [64319](#) , [64320](#) ,
[64321](#) , [64326](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for CP 0.635mm Female Terminals for CMC Connector, 0.22-0.35mm ² Wire Extraction Tool for 0.60mm CP Crimp Terminals for CMC Connector	638119100 638132400

Wire Size mm²	0.35	FineAdjust Applicator639021900 for 0.60mm CP Terminals, for 0.22mm², 0.35mm², 0.50mm² Metric Wires
Electrical		
Current - Maximum per Contact	6.0A	
Voltage - Maximum	14V DC	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Reference - Drawing Numbers		
Application Specification	AS-64318-002-001, AS-64318-002-CH-001, AS-64318-002-FR-001, AS-64318-002-SP-001, AS-64319-002-001, AS-64319-002-CH-001, AS-64319-002-FR-001, AS-64319-002-SP-001, AS-64322-001-001, AS-64322-001-CH-001, AS-64322-001-FR-001, AS-98420-001-001, AS-98420-001-CH-001, AS-98420-001-FR-001, AS-98420-001-SP-001, AS-98420-002-001, AS-98420-002-CH-001, AS-98420-002-FR-001, AS-98420-002-SP-001	
Crimp Specification	CS-64322-001-001	
Packaging Specification	313025040-000, PK-98913-001-001	
Product Specification	PS-64319-002-001, PS-64326-001-001	
Sales Drawing	SD-64322-001-000	

This document was generated on 12/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[64322-1229](#)