

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0688014229](#)
Status: **Active**
Overview: Pico-EZmate and Pico-EZmate Plus Wire-to-Board Connector Systems
Description: Pico-EZmate-to-Pigtail Cable Assembly, 2 Circuits, 28 AWG fused to 18 AWG Pigtails, Stripped, Cable Length 0.458m

Documents:

3D Model	Product Specification PS-68801-002-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	

General

Product Family	Cable Assemblies
Series	666
Assembly Configuration	Single Ended Connector
Connector to Connector	Pico-EZmate-to-Pigtail
Overview	<u>Pico-EZmate and Pico-EZmate Plus Wire-to-Board Connector Systems</u>
Product Name	Pico-EZmate
UPC	887191283036

Physical

Cable Length	0.458m
Circuits (Loaded)	2
Color - Resin	White
Gender	Male-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	Nylon Alloy
Net Weight	9.300/g
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	UL 1371 VW-1 Fused to UL 1569

Electrical

Current - Maximum per Contact	2.8A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Product Specification	PS-68801-002-001
Sales Drawing	SD-68801-094



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[666 Series](#)

Mates With

Bridgelux Vero Array Holder

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[68801-4229](#)