

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0719731214

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid PCB Connector, Dual Row, Right-Angle, Early Entry Receptacle, with Flange, 28 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Packaging Specification PK-70873-0139-001 (PDF)


RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Receptacles
Series		71973
Application		Board-to-Board, Signal
Overview		C-Grid Connector Products
Product Name		C-Grid
UPC		800754691390
Physical		
Circuits (Loaded)		28
Circuits (maximum)		28
Color - Resin		Black
Durability (mating cycles max)		50
Flammability		94V-0
Glow-Wire Capable		No
Material - Metal		Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Number of Rows		2
Orientation		Right Angle
PC Tail Length		3.05mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		3.05mm
Packaging Type		Tube
Pitch - Mating Interface		2.54mm
Plating min - Mating		1.270µm
Plating min - Termination		2.540µm
Polarized to PCB		No
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		Through Hole

Electrical		
Current - Maximum per Contact		2.0A
Voltage - Maximum		250V

Material Info

Reference - Drawing Numbers		
Packaging Specification		PK-70873-0139-001
Sales Drawing		SDA-71973-XXXX



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

71973 Series

Mates With

70204

This document was generated on 03/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[71973-1214](#)