

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0733660020

Status:

Active

Overview:

MCX RF Connectors

Description:

50 Ohm MCX Plug, Crimp, RG-174, RG-188 and RG-316 Cable, 0.25µm Gold (Au) Plated Center Contact, Nickel (Ni) Plated Body, Bag

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Name

Style

Type

UPC

Wire/Cable Type

RF/Coax Connectors

73366

MCX RF Connectors

MCX

Cable

Microminiature

800754245739

RG-174, RG-188, RG-316

Physical

Cable Attachment

Gender

Keying to Mating Part

Net Weight

Orientation

PCB Mounting

Packaging Type

Panel Mount

Panel Mount Method

Reverse Polar

Crimp

Plug

None

1.284/g

Straight

N/A

Bag

No

N/A

No

Electrical

Frequency

Impedance

Power / Voltage

6 GHz

50Ω

VOLTAGE: 335 Vrms@Sea Level

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-73366-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73366 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73366-0020](#)