

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0733660061](#)
Status: **Active**
Overview: [MCX RF Connectors](#)
Description: 50 Ohms, MCX Jack Receptacle, Vertical, Straight, 7.10mm Height, 1.57mm Standoff Height, Gold (Au) Plated Body, Tray

Documents:
[3D Model](#) [Drawing \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family RF/Coax Connectors
Series [73366](#)
Overview [MCX RF Connectors](#)
Product Name MCX
Style PCB
Type Microminiature
UPC 800756205649
Wire/Cable Type N/A

Physical
Gender Jack
Keying to Mating Part None
Net Weight 0.560/g
Orientation Straight
PCB Mounting Through Hole
PCB Thickness - Recommended 1.20mm
Packaging Type Tray
Panel Mount No
Panel Mount Method N/A
Reverse Polar No

Electrical
Frequency 6 GHz
Impedance 50Ω
Power / Voltage VOLTAGE: 335 Vrms@Sea Level

Solder Process Data
Duration at Max. Process Temperature (seconds) 010
Lead-freeProcess Capability REFLOW
Max. Cycles at Max. Process Temperature 002
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers
Sales Drawing SD-73366-006-001, SD-73366-619-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)9139-DC (19 Jan 2021)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[73366](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73366-0061](#)