

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

74506-3002

Status:

Active

Overview:

LaneLink™

Description:

0.50mm Pitch LaneLink™ InfiniBand* Cable Assembly, Non-Equalized, 28 AWG, 4X, 1.0m Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Test Summary TS-74506-001 (PDF)

Agency Certification	
UL	E72548
General	
Product Family	Cable Assemblies
Series	74506
Assembly Configuration	Dual Ended Connectors
Connector to Connector	InfiniBand* 4x Both Ends
Overview	LaneLink™
Product Name	4X, InfiniBand*, LaneLink™
UPC	756054497999
Physical	
Cable Length	1.0m
Circuits (Loaded)	4X
Flammability	94V-0
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	145.427/g
Packaging Type	Bag
Single Ended	No
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Twin-ax
Electrical	
Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	30V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-74506-300
Test Summary	TS-74506-001

*InfiniBand is a trademark of the InfiniBand Trade Association.

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74506Series

Mates With

91525 4X/12X Latch LaneLink™ Receptacle. 91804 LaneLink™ Connector

Use With

74735 X2 Transceiver. 74739 XPAK Transceiver

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[74506-3002](#) [74506-3001](#)