

Part Number:	0745460406
Status:	Active
Overview:	iPass Connector System
Description:	iPass PCIe x4 Cable Assembly, 24 AWG, 6.0m Length

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

CSA	LR64395
UL	E72548

Product Family	Cable Assemblies
Series	<u>74546</u>
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PCI Express-to-PCI Express
Overview	<u>iPass Connector System</u>
Product Name	iPass, PCI Express
UPC	822348864874

Cable Length	6.0m
Circuits (Loaded)	38
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Net Weight	780.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Waterproof / Dustproof	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	24
Wire/Cable Type	Round

Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V DC

Reference - Drawing Numbers
Sales Drawing SD-74546-400



Series image - Reference only

Not Relevant

Compliant

Contained Per -
D(2020)4578-DC (25
June 2020)

C,C'-
azodi(formamide)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

74546 Series

Mates With

75586 iPass Receptacle

Use With

74540 PCIe Guide Frame

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74546-0406