

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745460807](#)
Status: **Active**
Overview: [iPass Connector System](#)
Description: iPass PCIe x8 Cable Assembly, 24 AWG, 7.0m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR64395
UL	E72548
General	
Product Family	Cable Assemblies
Series	74546
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PCI Express-to-PCI Express
Overview	iPass Connector System
Product Name	iPass, PCI Express
UPC	822350025881
Physical	
Cable Length	7.0m
Circuits (Loaded)	68
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Net Weight	4525.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	24
Wire/Cable Type	Round
Electrical	
Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-74546-800-001



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Green Image Not Relevant Not Contained	

Search Parts in this Series
[74546](#) Series

Mates With
[75586](#) iPass Receptacle

Use With
[74540](#) PCIe Guide Frame

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74546-0807](#)