

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745464082](#)
Status: **Active**
Overview: [iPass Connector System](#)
Description: 0.80mm Pitch iPass PCI Express X4-to-X8 Transition Cable Assembly, 2.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	74546
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PCI Express-to-PCI Express
Overview	iPass Connector System
Product Name	iPass, PCI Express
UPC	800756824949

Physical

Cable Length	2.0m
Circuits (Loaded)	68
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Net Weight	1.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	0.80mm
Single Ended	No
Waterproof / Dustproof	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	24, 26, 28
Wire/Cable Type	Round

Electrical

Current - Maximum per Contact	1.0A
Shield Type	Upper Shielding
Shielded	Yes
Voltage - Maximum	30V DC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-74546-408-001
---------------	------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

C,C'-
azodi(formamide)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74546](#) Series

Mates With

[75586](#) iPass Receptacle. [741500001](#) SMT Receptacle

Use With

[74540](#) PCIe Guide Frame

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74546-4082