

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0747521208
Status: Active
Overview: SFP+ and SFP Interconnect Solutions
Description: SFP+-to-SFP+ Lite Passive Cable Assembly, 10Gbps, 30 AWG Cable, with Latch, 2.0m Length



Series image - Reference only

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR64395
UL	E72548
General	
Product Family	Cable Assemblies
Series	74752
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	SFP+-to-SFP+
Overview	SFP+ and SFP Interconnect Solutions
Product Name	SFP Plus, SFP+
UPC	889056311694
Physical	
Cable Length	2.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	94.491/g
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Wire Size AWG	30
Wire/Cable Type	Twinax
Electrical	
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Material Info	
Reference - Drawing Numbers	
Sales Drawing	747520008-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

74752 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74752-1208