

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747642301](#)
Status: **Active**
Overview: [SFP+ and SFP Interconnect Solutions](#)
Description: QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 28 AWG Cable, Pull-to-Release Plunger Style Latch, 3.0m Length

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	74764
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	QSFP+-to-4 SFP+
Overview	SFP+ and SFP Interconnect Solutions
Product Name	QSFP Plus, QSFP+, SFP Plus, SFP+
UPC	884982451599

Physical

Cable Length	3.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	512.600/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Twinax

Electrical

Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes

Material Info

Reference - Drawing Numbers

Sales Drawing	747640001-000
---------------	---------------



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

China RoHS

Contained Per -
D(2021)4569-DC (8
July 2021)
Diboron-trioxide
Bisphenol-A
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[74764 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[74764-2301](#)