

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0758380204](#)
Status: **Active**
Overview: [GbX Backplane Connector System](#)
Description: GbX 4 Pair Backplane Connector System Open Header, 200 Circuits, 25 Columns, Gold (Au) 0.76µm, Pin Length 4.55mm, Lead-Free

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-75221-999-001 \(PDF\)](#)
[Packaging Specification PK-70873-563 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


UL E29179

General

Product Family Backplane Connectors
Series [75838](#)
Application Backplane
Application Tooling Documents TM-622022099
Comments Open Header, Open Header
Component Type Power Header
Overview [GbX Backplane Connector System](#)
Product Name GbX
UPC 800756802534

Physical

Circuits (Loaded) 200
Circuits (maximum) 200
Color - Resin Gray
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part No
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 11.890/g
Number of Columns 25
Number of Pairs 4
Number of Rows 8
Orientation Vertical
PC Tail Length 2.30mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.85mm
Pitch - Termination Interface 1.85mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to PCB No
Stackable Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating 105°C
Termination Interface: Style Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[75838](#) Series

Mates With

[75878](#) Daughtercard Assembly

Electrical

Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-70873-563
Product Specification	PS-75221-999-001
Sales Drawing	SD-75838-010

This document was generated on 12/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75838-0204](#)