

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0760105141

Status:


Active

Overview:

iPass Connector System

Description:

0.80mm Pitch iPass I/O Connector Shell, Right-Angle, Through Hole 3.56mm, 36 Circuits, Left Key



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Packaging Specification PK-76010-001 \(PDF\)](#)

General	
Product Family	I/O Connectors
Series	76010
Application	Wire-to-Board
Component Type	Shell Body
Material - Shield/Shell	Copper-Nickel-Zinc
Overview	iPass Connector System
Product Name	iPass
Type	N/A
UPC	822350614306
Physical	
Boot Color	N/A
Circuits (Loaded)	N/A
Circuits (maximum)	36
Circuits Detail	36
Durability (mating cycles max)	25
Gender	N/A
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Zinc
Material - Plating Mating	N/A
Net Weight	0.847/g
Number of Rows	0
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +80°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	N/A
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	N/A
Solder Process Data	
Duration at Max. Process Temperature (seconds)	020

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76010 Series

Mates With

79575 iPass Internal Cable, 74563 iPass Mini-SAS Internal Cable, 79576 iPass 36 Circuit-SATA Fanout Cable, 74573 iPass 36 Circuit RA-SATA Cable, 79536 iPass 36 Circuit SATA Cable, 74562 iPass 36 Circuit Right Angle

Use With

75586 0.80mm Pitch iPass I/O Connector

Lead-free	Process Capability	REFLOW
Max. Cycles at Max. Process Temperature		001
Process Temperature max. C		260
Material Info		
Reference - Drawing Numbers		
Packaging Specification		PK-76010-001
Sales Drawing		SD-76010-001-001

This document was generated on 04/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76010-5141](#)