

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0760605010

Status:

Active

Overview:

Impact Backplane Connector and Cable Assembly System

Description:

Impact 100 Ohm 5 Pair Right-Angle Daughtercard Receptacle, Right Guided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free

Documents:

- 3D Model

Application Specification AS-76060-9999-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-70873-611-001 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-76060-5010-001 (PDF)
- Product Specification PS-76060-999-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-76060-990-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Backplane Connectors

Series

76060

Application

Conventional, Daughtercard

Application Tooling Documents

TM-622018799-001

Component Type

PCB Receptacle

Electrical Model

Yes

Overview

Impact Backplane Connector and Cable Assembly System

Product Name

Impact

UPC

883906421717

Physical

Circuits (Loaded)

150

Circuits (maximum)

150

Color - Resin

Black

Durability (mating cycles max)

200

First Mate / Last Break

No

Flammability

94V-0

Guide to Mating Part

Yes

Keying to Mating Part

None

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

21.958/g

Number of Columns

10

Number of Pairs

5

Number of Rows

15

Orientation

Right Angle

PC Tail Length

1.20mm

PCB Locator

No

PCB Retention

Yes

PCB Thickness - Recommended

1.00mm

Packaging Type

Tray

Pitch - Mating Interface

1.90mm

Pitch - Termination Interface

1.90mm

Plating min - Mating

0.762µm

Polarized to PCB

No

Stackable

No

Temperature Range - Operating

-55° to +85°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76060 Series

Mates With

76055 Impact 100 Ohm Vertical Backplane Header

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-76060-990-001, AS-76060-9999-001
Electrical Model Document	EE-76060-003-001
Packaging Specification	PK-70873-611-001
Product Specification	PS-76060-999-001
S-Parameter Model	SP-76060-003-001
Sales Drawing	SD-76060-004-001
Symbol/Footprint Data	SYM-76060-5010-001

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76060-5010](#)