

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0765301040

Status:

Active

Overview:

Impact Backplane Connector and Cable Assembly System

Description:

Impact 100 Ohm 5 Pair Mezzanine Receptacle, 40mm Stack Height, Unguided, 10 Columns, 150 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free

Documents:

- 3D Model

Application Specification AS-76060-9999-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-70873-0040-001 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-76530-1040-001 (PDF)
- Product Specification PS-76060-999-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification AS-76060-990-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Backplane Connectors

Series

76530

Application

Mezzanine

Application Tooling Documents

TM-622018799-001

Component Type

PCB Receptacle

Overview

Impact Backplane Connector and Cable Assembly System

Product Name

Impact

UPC

884982220423

Physical

Circuits (Loaded)

150

Circuits (maximum)

150

Color - Resin

Black

Durability (mating cycles max)

200

First Mate / Last Break

No

Flammability

94V-0

Guide to Mating Part

No

Keying to Mating Part

None

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

21.430/g

Number of Columns

10

Number of Pairs

5

Number of Rows

15

Orientation

Vertical

PC Tail Length

1.20mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

1.90mm

Pitch - Termination Interface

1.90mm

Plating min - Mating

0.762µm

Polarized to PCB

No

Stackable

Yes

Temperature Range - Operating

-55° to +85°C

Termination Interface: Style

Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76530 Series

Mates With

76055 Impact 100 Ohm 5 Pair Vertical
Backplane Header

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-76060-990-001, AS-76060-9999-001
Electrical Model Document	EE-76530-0040-001
Packaging Specification	PK-70873-0040-001
Product Specification	PS-76060-999-001
S-Parameter Model	SP-76530-0028-002, SP-76530-0038-002, SP-76530-0040-001
Sales Drawing	SD-76530-001-001
Symbol/Footprint Data	SYM-76530-1040-001

This document was generated on 09/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76530-1040](#)