

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0768661013](#)
Status: **Active**
Overview: [iPass+ HD Interconnect System](#)
Description: [iPass+ HD Cage and Receptacle 1x4, 0.76μm, Lead-Free](#)

Documents:

3D Model	Application Specification AS-76866-002-001 (PDF)
Drawing (PDF)	Packaging Specification PK-76866-001-001 (PDF)
3D Model (PDF)	Test Summary TS-76866-001-001 (PDF)
Product Specification PS-76866-001-001 (PDF)	Test Summary TS-76866-1004-001 (PDF)
Application Specification AS-76866-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E107635

General


Product Family	I/O Connectors
Series	76866
Application	Wire-to-Board
Component Type	External Integrated Cage, Receptacle
Electrical Model	Yes
Overview	iPass+ HD Interconnect System
Product Name	iPass+
Type	N/A
UPC	887191048864

Physical

Circuits (Loaded)	144
Circuits (maximum)	144
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	26.796/g
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.75mm
Pitch - Termination Interface	0.75mm
Plating min - Mating	0.762μm
Plating min - Termination	0.762μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +80°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	0.75A
Voltage - Maximum	30V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76866](#) Series

Mates With

iPass Cable Assembly [111068](#) , [111075](#) ,
[111077](#)

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-76866-001-001, AS-76866-002-001

Electrical Model Document EE-76866-1004-001

Packaging Specification PK-76866-001-001

Product Specification PS-76866-001-001

S-Parameter Model SP-76866-100-001, SP-76866-1004-001

Sales Drawing SD-76866-1000-001

Test Summary TS-76866-001-001, TS-76866-1004-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76866-1013](#)