


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0787570001](#)  
**Status:** **Active**  
**Overview:** [Serial Attached SCSI \(SAS\) Connectors](#)  
**Description:** 1.27mm Signal Pitch, 0.80mm Signal Pitch, 1.27mm Power Pitch SAS-3/PCIe-3 Receptacle, Vertical, Surface Mount, with Front Solder Tab, 8.15mm Height, 2.00mm Peg Length, 2.36mm Peg Diameter, 1.60mm PCB Thickness, 68 Circuits, with Cap, Embossed Tape and Reel, Lead-Free



Series image - Reference only

|                                                              |                                                                  |
|--------------------------------------------------------------|------------------------------------------------------------------|
| <b>Documents:</b>                                            |                                                                  |
| <a href="#">3D Model (PDF)</a>                               | <a href="#">Application Specification AS-78757-001-001 (PDF)</a> |
| <a href="#">3D Model</a>                                     | <a href="#">Packaging Specification PK-78757-001-001 (PDF)</a>   |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Test Summary TS-78757-001-001 (PDF)</a>              |
| <a href="#">Product Specification PS-78757-001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                  |                                                       |
|------------------|-------------------------------------------------------|
| Product Family   | I/O Connectors                                        |
| Series           | <a href="#">78757</a>                                 |
| Application      | Board-to-Board                                        |
| Comments         | With Cap                                              |
| Component Type   | Receptacle                                            |
| Electrical Model | Yes                                                   |
| Overview         | <a href="#">Serial Attached SCSI (SAS) Connectors</a> |
| Product Name     | SAS-3/PCIe-3, U.2 (SFF-8639)                          |
| Type             | N/A                                                   |
| UPC              | 887191240602                                          |

**Physical**

|                                |                        |
|--------------------------------|------------------------|
| Circuits (Loaded)              | 68                     |
| Circuits Detail                | Signal 53, Power 15    |
| Color - Resin                  | Black                  |
| Durability (mating cycles max) | 500                    |
| Flammability                   | 94V-0                  |
| Gender                         | Female                 |
| Keying to Mating Part          | Yes                    |
| Lock to Mating Part            | None                   |
| Material - Metal               | Copper Alloy           |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 1.887/g                |
| Number of Rows                 | 2                      |
| Orientation                    | Vertical               |
| PCB Locator                    | Yes                    |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.60mm                 |
| Packaging Type                 | Embossed Tape on Reel  |
| Panel Mount                    | No                     |
| Pitch - Mating Interface       | 0.80mm, 1.27mm         |
| Pitch - Termination Interface  | 0.80mm, 1.27mm         |
| Plating min - Mating           | 0.762µm                |
| Plating min - Termination      | 2.540µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[78757](#) Series

**Mates With**

U.2 (SFF-8639) Plug [78758](#) , SAS / SATA  
Plugs

|                                                |                                    |
|------------------------------------------------|------------------------------------|
| Surface Mount Compatible (SMC)                 | Yes                                |
| Temperature Range - Operating                  | 0° to +55°C                        |
| Termination Interface: Style                   | Surface Mount                      |
| <b>Electrical</b>                              |                                    |
| Current - Maximum per Contact                  | 1.5A                               |
| Voltage - Maximum                              | 30V                                |
| <b>Solder Process Data</b>                     |                                    |
| Duration at Max. Process Temperature (seconds) | 010                                |
| Lead-freeProcess Capability                    | REFLOW                             |
| Max. Cycles at Max. Process Temperature        | 001                                |
| Process Temperature max. C                     | 260                                |
| <b>Material Info</b>                           |                                    |
| <b>Reference - Drawing Numbers</b>             |                                    |
| Application Specification                      | AS-78757-001-001                   |
| Electrical Model Document                      | EE-78757-001-001, EE-78757-002-001 |
| Packaging Specification                        | PK-78757-001-001                   |
| Product Specification                          | PS-78757-001-001                   |
| S-Parameter Model                              | SP-78757-001-001, SP-78757-002-001 |
| Sales Drawing                                  | SD-78757-001-000                   |
| Signal Integrity Report                        | SI-78757-001-001                   |
| Test Summary                                   | TS-78757-001-001                   |

This document was generated on 10/05/2021

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78757-0001](#)