

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0795405015](#)
Status: **Active**
Overview: [In-Vehicle Smart Charging Modules](#)
Description: In-Vehicle Single Port USB Battery Charger with Backlight, 1.0A

Documents:

3D Model	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	Product Literature (PDF)
Drawing (PDF)	

General

Product Family	I/O Connectors
Series	79540
Application	Module-to-Wire
Component Type	USB Charger
Overview	In-Vehicle Smart Charging Modules
Product Name	Micro-Fit 3.0, USB
Type	A
UPC	887191430973

Physical

Circuits (Loaded)	3
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	5000
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	ABS, PC
Net Weight	23.200/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	16V DC

Material Info

Reference - Drawing Numbers	
Sales Drawing	SD-79540-5015-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

**Compliant with
Exemption 7(c)-
I,7(a)***

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)*

Halogen-Free

Status

Not Low-Halogen*

For more information, please visit [Contact US](#)

CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from
CUST_NOTE2	product compliance status evaluation.
China ROHS	50 Image
ELV	Not Reviewed
RoHS Phthalates	Not Contained*

Search Parts in this Series

[79540](#) Series

Mates With

USB Type A (Front)
Micro-Fit 3.0
Receptacle [436450500](#) (Rear)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[79540-5015](#)