

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0797580008
Status: Active
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead Pico-SPOX Female-to-Pico-SPOX Female, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series 79758
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Pico-SPOX Crimp Terminals
Overview Off-the-Shelf Pre-Crimped Leads
Product Name Pico-SPOX
UPC 884982052710

Physical

Cable Length 150.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Female-Female
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.494/g
Packaging Type Bag
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Size AWG 24
Wire/Cable Type UL 1061

Material Info

Reference - Drawing Numbers
Sales Drawing SD-797580001



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
79758 Series

Use With
Pico-SPOX Housings 87439

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[79758-0008](#)