

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0834149021

Status:

Active

Overview:

Commercial Micro-D High-Density Connectors

Description:

1.27mm Pitch Commercial Micro-D Panel Mount Header, 25 Circuits

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	83414
Application	Wire-to-Wire
Component Type	Panel Mount Header
Overview	Commercial Micro-D High-Density Connectors
Product Name	Commercial Micro-D
Type	N/A
UPC	822350302005
Physical	
Circuits (Loaded)	N/A
Circuits (maximum)	25
Durability (mating cycles max)	Contact Molex
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Panel Mount	Yes
Pitch - Mating Interface	0.64mm
Pitch - Termination Interface	0.64mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Ports	1
Surface Mount Compatible (SMC)	No
Termination Interface: Style	N/A
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	N/A
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	N/A

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
83414 Series

Mates With
83424 Commercial Micro-D Cable Assemblies, 24 Circuits

Use With
830009560 Commercial MicroD Pin Terminal, .381µm Gold, Loose Piece,
830009561 Commercial MicroD Pin Terminal, .381µm Gold, 2500 Piece Reel

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[83414-9021](#)