

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0834219037

Status:

Active

Overview:

Commercial Micro-D High-Density Connectors

Description:

Commercial Micro-D, CMD-to-D-Sub, 9 Circuits, Female - Male, 0.91m Length

Documents:

Drawing (PDF)

Product Specification PS-83421-001-001 (PDF)

Packaging Specification PK-83422-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Assembly Configuration

Connector to Connector

Overmolded

Overview

Product Name

UPC

Cable Assemblies

83421

Dual Ended Connectors

Commercial Micro-D-to-D-Sub

Yes

Commercial Micro-D High-Density Connectors

Commercial Micro-D, D-Sub

800756424583

Physical

Cable Length

Circuits (Loaded)

Gender

Lock to Mating Part

Material - Plating Termination

Net Weight

Number of Rows

Packaging Type

Plating min - Mating

Plating min - Termination

Single Ended

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

0.91m

9

Male-Female

None

Tin

0.569/g

2

Bag

0.127µm

1.270µm

No

Crimp or Compression

N/A

28

PVC

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-83422-001-001

PS-83421-001-001

SD-83421-021-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS
Compliant with
Exemption 6(a)-I
REACH SVHC

China RoHS

Contained Per -
D(2020)9139-DC (19
Jan 2021)
heptacosafuorotetradecanoic
acid
Dodecamethylcyclhexasiloxane
Octamethylcyclotetrasiloxane
methoxyacetic acid
1,2-diethoxyethane
2-methylimidazole
1-vinylimidazole
1,3-Propanesultone
henicosafuoroundecanoic
acid
sodium
peroxometaborate
1,7,7-trimethyl-3-
(phenylmethylene)bicyclo[2.2.1
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
diisohexyl phthalate
pentacosafuorotridecanoic
acid
2-Methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop
4,4-
isobutylethylidenediphenol
2-benzyl-2-
dimethylamino-4-
morpholinobutyropheno
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
Hydrazine
Disodium tetraborate

Boric acid
Trixylyl phosphate
2,3,3,3-tetrafluoro-2-(heptafluoropropoxy)propio
Tris(4-nonylphenyl, branched and linear)
phosphi
Fluoranthene
Pyrene
Diocetyl tin dilaurate, stannane, dioctyl-, bis(co
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
Methylhexahydrophthalic anhydride
Sodium perborate; perboric acid, sodium salt
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5
Perfluorohexane-1-sulphonic acid and its salts
Arsenic acid
(H₃AsO₄), triethyl ester
Dibutylphthalate
Di-(2-ethylhexyl)phthalat
Butylbenzylphthalate
2,4-Dinitrotoluene
Diisobutyl-phthalate
Boric acid, disodium salt, hydrate
Trichloroethylene
1-Methyl-2-pyrrolidone
formamide
4,4'-bis(dimethylamino)benzophenone
N,N,N',N'-tetramethyl-4,4'-methylenedianiline
1,2-bis(2-methoxyethoxy)ethane
4,4'-bis(dimethylamino)-4''-(methylamino)trityl
Diboron-trioxide
 α,α' -Bis[4-(dimethylamino)phenyl]-4(phenylamino)
Lead
Cadmium-chloride
Silicic acid (H₂Si₂O₅), barium salt (1:1), lead-diethyl sulphate
propylene oxide

Acetamide, N-methyl-
Phenanthrene
Dinoseb
butyl 4-
hydroxybenzoate
4-tert-butylphenol
nitrobenzene
Ethylenediamine
furan
2-Methoxyethyl
acetate
C,C'-
azodi(formamide)
bis(2-(2-
methoxyethoxy)ethyl)
ether
tricosafuorododecanoic
acid

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

83421 Series

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

83421-9037