

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0845860018
Status: Active
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Terminator Resistor, Male 5 Poles, meets NMEA 2000



Series image - Reference only

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series 84586
IP Rating IP67
Material - Contact Copper Alloy
Overview Brad Micro-Change (M12) Connectors
Product Name Micro-Change (M12)
Type Termination Resistor
UPC 822350898287

Physical
Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender Male
Keyway Single
Material - Connector Body PVC
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Net Weight 44.000/g
Orientation Straight
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum N/A

Material Info
Engineering Number NMEA-DND100NB

Reference - Drawing Numbers
Sales Drawing SD-84586-008-001

EU ELV

Not Relevant

EU RoHS

Compliant with
Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

84586 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[84586-0018](#) [NMEA-DND100NB](#)