

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0847271003
Status: Active
Overview: Sealed Industrial USB Solutions
Description: Sealed Industrial USB Type A Plug-to-Shielded Pigtail, 3.0m Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84727-002-001 \(PDF\)](#)

General
Product Family Cable Assemblies
Series 84727
Assembly Configuration Single Ended Connector
Comments Fully shielded for EMI/RFI protection
Connector to Connector USB Type A-to-Pigtail
Overview Sealed Industrial USB Solutions
Product Name Industrial USB
UPC 822348847679

Physical
Cable Length 3.0m
Circuits (Loaded) 5
Color - Resin Black
Gender Plug
Lock to Mating Part None
Material - Resin Polyester, PVC
Packaging Type Bag
Pitch - Mating Interface 2.00mm, 2.50mm
Single Ended Yes
Waterproof / Dustproof Yes
Waterproof / Dustproof Type IP67
Wire Insulation Diameter N/A
Wire Size AWG N/A
Wire/Cable Type USB

Electrical
Current - Maximum per Contact 1.0A
Impedance Non-constant
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 30V AC (RMS)

Material Info

Reference - Drawing Numbers
Product Specification PS-84727-002-001



EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Contained Per - ED/108/2014 (17 Dec 2014)	
bis(2-ethylhexyl) phthalate (DEHP)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
84727 Series

Mates With
84729 Sealed Industrial USB 2.0 Type A Panel Mount PCB Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84727-1003](#)