

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0847281002

Status:

Active

Overview:

Sealed Industrial USB Solutions

Description:

Sealed Industrial USB Type B Plug-to-Shielded Pigtail, 1.50m Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	84728
Assembly Configuration	Single Ended Connector
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type B-to-Pigtail
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	822348847624
Physical	
Cable Length	1.50m
Circuits (Loaded)	5
Color - Resin	Black
Gender	Plug
Lock to Mating Part	None
Material - Resin	Polyester, PVC
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	Yes
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire/Cable Type	USB
Electrical	
Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Sales Drawing	847281001-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

84728 Series

Mates With

84730 Sealed Industrial USB 2.0 Type B
Panel Mount PCB Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84728-1002](#)