

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0847290001](#)
Status: **Active**
Overview: [Sealed Industrial USB Solutions](#)
Description: Sealed Industrial USB 2.0 Type A Receptacle-to-Pigtail, Neoprene Gasket, 28 AWG, 0.152M Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84727-002-001 \(PDF\)](#)

General
Product Family Cable Assemblies
Series [84729](#)
Assembly Configuration Single Ended Connector
Comments Fully shielded for EMI/RFI protection
Connector to Connector USB Type A-to-Pigtail
Overview [Sealed Industrial USB Solutions](#)
Product Name Industrial USB
UPC 822348842155

Physical
Cable Length 0.152m
Circuits (Loaded) 4
Color - Resin Black
Gender Female-Pigtail
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Gold
Material - Resin PBT
Net Weight 125.000/g
Number of Rows 1
Packaging Type Bag
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Single Ended Yes
Waterproof / Dustproof Yes
Waterproof / Dustproof Type IP67, NEMA 6P
Wire Size AWG 28
Wire/Cable Type USB

Electrical
Current - Maximum per Contact 1.0A
Impedance 90Ω
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 30V AC (RMS)

Material Info

Reference - Drawing Numbers
Product Specification PS-84727-002-001
Sales Drawing SD-84729-005-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

**Missing Compliance
Data**

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[84729 Series](#)

Mates With

Industry Standard Bayonet Locking USB
Type A Plug

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

84729-0001