

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0847290015
Status: Active
Overview: Sealed Industrial USB Solutions
Description: Sealed Industrial USB 2.0 Type A Receptacle-to-Pigtail, Neoprene Gasket, 20 AWG, 1.10M Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable Assemblies
Series 84729
Assembly Configuration Single Ended Connector
Comments Fully shielded for EMI/RFI protection
Connector to Connector USB Type A-to-Pigtail
Overview Sealed Industrial USB Solutions
Product Name Industrial USB
UPC 884982789500

Physical
Cable Length 1.10m
Circuits (Loaded) 4
Color - Resin Black
Gender Female-Pigtail
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Gold
Material - Resin PBT
Number of Rows 1
Packaging Type Bag
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Single Ended Yes
Waterproof / Dustproof Yes
Waterproof / Dustproof Type IP67, NEMA 6P
Wire Size AWG 20
Wire/Cable Type USB

Electrical
Current - Maximum per Contact 1.0A
Impedance 90Ω
Shield Type Full Shield
Shielded Yes
Voltage - Maximum 30V AC (RMS)

Material Info

Reference - Drawing Numbers
Sales Drawing SD-84729-005-000



EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/108/2014 (17 Dec 2014)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
84729 Series

Mates With
Industry Standard Bayonet Locking USB Type A Plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84729-0015](#)