

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0848599004

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change Molded Junction Box, Top-Mount with Molded Cable, 4 Ports, 3.00m Length Cable



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Passive Distribution Boxes
Series	84859
IP Rating	IP68
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
UPC	822350925679

Physical	
Bus I/O	Micro-Change (M12)
Cable Connector Orientation	Straight
Cable Length	3.0m
Home Run Cable Length	N/A
Home Run Connector	N/A
Home Run Interface	N/A
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Housing	PBT
Material - Metal	Brass
Material - Plating Mating	Gold
Orientation	Top-Mount
Poles	5
Poles (wired)	5
Ports	4
Temperature Range - Operating	-25°C to +90°C
Wiring Configuration	Single I/O per Port

Electrical	
Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	Parallel
Voltage - Maximum	10-30V DC

Material Info	
Engineering Number	NMEA-DND4500NB-030

Reference - Drawing Numbers	
Sales Drawing	SD-84859-001-001

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

84859 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84859-9004](#)