

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850030282

Status:

Active

Overview:

DIN 41612

Description:

DIN 41612 Header, Style C, 64 Circuits, Lead-Free

Documents:


3D Model

Drawing (PDF)

Product Specification PS-85003-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Backplane Connectors
Series		85003
Application		Backplane
Component Type		PCB Header
Overview		DIN 41612
Product Name		IEC 603-2/DIN 41612
Style		C
UPC		800753240322
Physical		
Circuits (Loaded)		64
Circuits (maximum)		96
Durability (mating cycles max)		500
First Mate / Last Break		No
Flammability		94V-0
Guide to Mating Part		No
Keying to Mating Part		Yes
Material - Plating Mating		Gold
Number of Columns		16
Number of Pairs		Open Pin Field
Number of Rows		3
Orientation		Right Angle
PC Tail Length		3.00mm
PCB Locator		No
PCB Retention		Yes
PCB Thickness - Recommended		1.60mm
Packaging Type		Tray
Pitch - Mating Interface		2.54mm
Pitch - Termination Interface		2.54mm
Polarized to PCB		Yes
Temperature Range - Operating		-55° to +125°C
Termination Interface: Style		Through Hole
Electrical		
Current - Maximum per Contact		2.5A
Data Rate		622.0 Mbps
Voltage - Maximum		250V AC (RMS)
Material Info		
Reference - Drawing Numbers		
Product Specification		PS-85003-0001-001
Sales Drawing		SD-85003-0282



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

85003 Series

Mates With

85042 , 85052 Backplane Header

This document was generated on 09/14/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85003-0282](#)