

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0850130438

Status:

Active

Overview:


DIN 41612

Description:

2.54mm Pitch DIN 41612 Header, Vertical, Style R Reverse, 1µm Selective Gold (Au), 96 Circuits, Lead-Free

Documents:	
3D Model	Product Specification PS-85013-0001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Backplane Connectors
Series	85013
Application	Backplane
Component Type	PCB Header
Overview	DIN 41612
Product Name	IEC 603-2/DIN 41612
Style	R
UPC	800753240247
Physical	
Circuits (Loaded)	96
Circuits (maximum)	96
Circuits Detail	Rows A, B, & C
Durability (mating cycles max)	500
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Net Weight	10.658/g
Number of Columns	32
Number of Pairs	Open Pin Field
Number of Rows	3
Orientation	Vertical
PC Tail Length	4.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	1.016µm
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +125°C
Electrical	
Current - Maximum per Contact	1.0A
Data Rate	622.0 Mbps
Voltage - Maximum	1000V (RMS)
Solder Process Data	
Lead-freeProcess Capability	WAVE



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

85013 Series

Mates With

85042 DIN 41612 Receptacle. 85052 DIN 41612 Header

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-85013-0001

SD-85013-0438, SDA-85013-0001, SDA-85013-0438

This document was generated on 09/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85013-0438](#)