



|                                    |                              |
|------------------------------------|------------------------------|
| Temperature Range - Operating      | -55° to +125°C               |
| Termination Interface: Style       | Through Hole - Compliant Pin |
| <b>Electrical</b>                  |                              |
| Current - Maximum per Contact      | 1.0A                         |
| Data Rate                          | 622.0 Mbps                   |
| Voltage - Maximum                  | 250V AC (RMS)                |
| <b>Solder Process Data</b>         |                              |
| Lead-freeProcess Capability        | N/A                          |
| <b>Material Info</b>               |                              |
| <b>Reference - Drawing Numbers</b> |                              |
| Product Specification              | PS-85013-0002                |
| Sales Drawing                      | SDA-85015-0141               |

This document was generated on 09/18/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[85015-0141](#)