

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0873812438

Status:

Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch Milli-Grid Receptacle, Surface Mount, Top Entry, 0.051µm Gold (Au) Plating, with Locating Peg, 24 Circuits, Lead-Free

Documents:

- 3D Model

Packaging Specification 873810001-PK-000 (PDF)
- 3D Model (PDF)

Packaging Specification PK-87368-0001-001 (PDF)
- Drawing (PDF)

Brochure (PDF)
- Product Specification PS-87380-002-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 503940001-AS-000 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

87381

Application

Board-to-Board, Signal

Comments

With Pegs

Overview

Milli-Grid Connector System

Product Name

Milli-Grid

UPC

884982768383

Physical

Circuits (Loaded)

24

Circuits (maximum)

24

Color - Resin

Black

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

0.629/g

Number of Rows

2

Orientation

Vertical

PCB Locator

Yes

PCB Retention

None

Packaging Type

Tube

Pitch - Mating Interface

2.00mm

Pitch - Termination Interface

2.00mm

Plating min - Mating

0.051µm

Plating min - Termination

1.905µm

Polarized to PCB

Yes

Stackable

Yes

Surface Mount Compatible (SMC)

N/A

Temperature Range - Operating

-55° to +105°C

Termination Interface: Style

Surface Mount

Electrical

Current - Maximum per Contact

1.9A

Voltage - Maximum

125V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

87381 Series

Mates With

87758 Vertical, Through Hole, Stackable PCB Header, 87759 Vertical, Surface Mount, Stackable PCB Header, 87760 Right Angle, Through Hole, Stackable PCB Header, 87831 Vertical, Through Hole PCB Header, 87832 Vertical, Surface Mount PCB

Solder Process Data

Duration at Max. Process Temperature (seconds)	014
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	265

Material Info

Reference - Drawing Numbers

Application Specification	503940001-AS-000
Packaging Specification	873810001-PK-000, PK-87368-0001-001
Product Specification	PS-87380-002-001
Sales Drawing	SD-87381-XXXX-001

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87381-2438](#)