

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0887283600](#)
Status: **Active**
Overview: [USB Products and Solutions](#)
Description: Universal Serial Bus (USB) Shielded I/O Cable Assembly: A-to-Pigtail Full-Rated, 5.0m Length

Documents:
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General
Product Family Cable Assemblies
Series [68594](#)
Assembly Configuration Single Ended Connector
Comments Full-rated, Full-rated
Connector to Connector USB Type A-to-Pigtail
Overview [USB Products and Solutions](#)
Product Name USB
UPC 800754341813

Physical
Cable Length 5.0m
Circuits (Loaded) 4
Gender Male
Lock to Mating Part Yes
Net Weight 209.000/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 2.00mm, 2.50mm
Single Ended Yes
Wire Insulation Diameter N/A
Wire Size AWG 28
Wire/Cable Type Round

Electrical
Current - Maximum per Contact 1.0A
Shielded Yes

Material Info

Reference - Drawing Numbers
Sales Drawing SD-88738-001-001



Series image - Reference only

EU ELV
Compliant

EU RoHS Compliant REACH SVHC Not Contained Per - ECHA_01_2020 (16 January 2020 Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS Green Image ELV Compliant RoHS Phthalates Not Contained
---	---

Search Parts in this Series
[68594 Series](#)

Mates With
Universal Serial Bus (USB) Type A
Receptacle [67329](#) , [67230](#) , [89485](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[88728-3600](#)