

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0887328502](#)
Status: **Active**
Overview: [USB Products and Solutions](#)
Description: USB On-The-Go (OTG) Shielded I/O Cable Assembly, USB A-to-Mini B, USB 2.0, 0.80m Length, Black


Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-88732-009 \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	68768
Assembly Configuration	Dual Ended Connectors
Connector to Connector	USB Type A-to-Mini-B
Overview	USB Products and Solutions
Product Name	USB
UPC	800756208381
Physical	
Cable Length	0.80m
Circuits (Loaded)	5
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	41.034/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	0.80mm, 2.50mm
Plating min - Mating	0.762µm
Plating min - Termination	4.064µm
Single Ended	No
Termination Interface: Style	Through Hole
Wire Insulation Diameter	N/A
Wire Size AWG	28
Wire/Cable Type	Round

Electrical	
Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers	
Packaging Specification	PK-88732-009
Sales Drawing	SD-887328500-001



EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - ECHA_01_2020 (16 January 2020 Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	
China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[68768](#) Series

Mates With
USB On-The-Go (OTG) Mini-B Receptacle
[54819](#) , [48242](#) , [500075](#) , [67503](#). Universal
Serial Bus Shielded Receptacle Type
A [67329](#) , [67226](#) , [67230](#) , [89485](#).
[54366](#) Universal Serial Bus Shielded I/O
Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[88732-8502](#)