

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901420024](#)
Status: **Active**
Overview:
Description: 2.54mm Pitch C-Grid III Crimp Housing Dual Row, 24 Circuits, Black

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [90142](#)
Application Signal, Wire-to-Board
Overview [cgrid_iii](#)
Product Name C-Grid III
UPC 800753657458

Physical

Breakaway No
Circuits (maximum) 24
Color - Resin Black
Flammability 94V-1
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin PPO
Net Weight 1.643/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part Yes
Ports 0
Stackable No
Temperature Range - Operating -55° to +105°C

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Product Specification PS-99020-0001-001
Sales Drawing SD-90142-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

[90142](#) Series

Mates With

C-Grid III Header, Dual Row [90122](#) , [90130](#) ,
[90131](#)

Use With

C-Grid III Crimp Terminal [90119](#)
 C-
Grid III Pre-Crimped Lead [797582022](#) ,
[797582023](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[90142-0024](#)