

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0916273001](#)
Status: **Active**
Overview: [RAST Connector System](#)
Description: 5.00mm Pitch Appli-Mate RAST Power IDT Housing, Direct/Indirect, Female, 5 Circuits, Glow-Wire Capable, Fully Coded, Open End Walls

Documents:

[Drawing \(PDF\)](#)
[Product Specification 916270001-000 \(PDF\)](#)
[Application Specification 916270001-002 \(PDF\)](#)
[Packaging Specification 916270001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family IDT and Solder Connectors
Series [91627](#)
Crimp Quality Equipment Yes
Overview [RAST Connector System](#)
Product Name RAST Power
UPC 822348790579
Use With RAST Standard Interface

Physical

Circuits (Loaded) 5
Circuits (maximum) 5
Color - Resin Natural
Durability (mating cycles max) 10
Flammability 94V-2
Gender Female
Glow-Wire Capable Yes
Lock to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 3.463/g
Number of Rows 1
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 5.00mm
Pitch - Termination Interface 5.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +120°C
Termination Interface: Style IDT or Pierce
Wire Size AWG 18, 20, 22, 24

Electrical

Current - Maximum per Contact 6.0A
Voltage - Maximum 250V AC

Material Info

Reference - Drawing Numbers

Application Specification 916270001-002
Packaging Specification 916270001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

[91627](#) Series

Mates With

[93071](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
RAST Power Semi-Automatic IDC Machine	2166580300
Appli-Mate RAST 2.5 Power Manual Terminator	622030000
Hand Tool for Appli-Mate RAST Power Connectors	638276200

This document was generated on 08/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

91627-3001