

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0934442102](#)  
**Status:** **Active**  
**Overview:** [ML-XT Sealed Connection System](#)  
**Description:** ML-XT Sealed 3 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Grey

**Documents:**  
[3D Model](#) [Application Specification 934430010-A \(PDF\)](#)  
[Drawing \(PDF\)](#) [Packaging Specification 934430002-K \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification 934430010-P \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**  
UL E29179

**General**  
Product Family Crimp Housings  
Series [93444](#)  
Application Power, Signal, Wire-to-Wire  
Overview [ML-XT Sealed Connection System](#)  
Product Literature Order No 987651-0201  
Product Name ML-XT  
UPC 889056191425

**Physical**  
Circuits (maximum) 3  
Color - Resin Grey  
Gender Receptacle  
Glow-Wire Capable No  
Keying to Mating Part None  
Lock to Mating Part Yes  
Material - Resin Nylon  
Net Weight 6.892/g  
Number of Rows 2  
Packaging Type Bag  
Panel Mount No  
Pitch - Mating Interface N/A  
Polarized to Mating Part Yes  
Temperature Range - Operating -55° to +125°C

**Electrical**  
Current - Maximum per Contact 13.0A

**Material Info**

**Reference - Drawing Numbers**  
[Application Specification 934430010-A](#)  
[Packaging Specification 934430002-K](#)  
[Product Specification 934430010-P](#)  
[Sales Drawing 934430020-000](#)



Series image - Reference only

**EU ELV**  
**Not Relevant**

| <b>EU RoHS</b>                                                | <b>China RoHS</b> |
|---------------------------------------------------------------|-------------------|
| <b>Compliant</b>                                              |                   |
| <b>REACH SVHC</b>                                             |                   |
| Not Contained Per - ED/71/2019 (16 July 2019)                 |                   |
| <b>Halogen-Free Status</b>                                    |                   |
| <b>Low-Halogen</b>                                            |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Green Image       |
| ELV                                                           | Not Relevant      |
| RoHS Phthalates                                               | Not Contained     |

**Search Parts in this Series**  
[93444 Series](#)

**Mates With**  
[ML-XT Sealed 3 Circuit Plug Housing 934452102](#)

**Use With**  
[ML-XT Male \(Pin\) Terminal 845240004](#) (Nickel), [ML-XT Male \(Pin\) Terminal 845240014](#) (Selective Gold), [ML-XT 3 Circuit Receptacle Wedgelock 93447](#), [ML-XT Blind Cavity Plug 934941000](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93444-2102](#)