

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0934443201

Status:

Active

Overview:

ML-XT Sealed Connection System

Description:

ML-XT Sealed 4 Circuit Receptacle Housing, Pre-Assembled with Large Rear Seal and Cover, Black



Series image - Reference only

|                                                         |                                                             |
|---------------------------------------------------------|-------------------------------------------------------------|
| Documents:                                              |                                                             |
| <a href="#">3D Model</a>                                | <a href="#">Application Specification 934430010-A (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                          | <a href="#">Packaging Specification 934430002-K (PDF)</a>   |
| <a href="#">Drawing (PDF)</a>                           | <a href="#">RoHS Certificate of Compliance (PDF)</a>        |
| <a href="#">Product Specification 934430010-P (PDF)</a> | <a href="#">Product Literature (PDF)</a>                    |

|                               |                                |
|-------------------------------|--------------------------------|
| Agency Certification          |                                |
| UL                            | E29179                         |
| Application tooling part link |                                |
| Application Tooling Part Link | 63824-5300                     |
| General                       |                                |
| Product Family                | Crimp Housings                 |
| Series                        | 93444                          |
| Application                   | Power, Signal, Wire-to-Wire    |
| Overview                      | ML-XT Sealed Connection System |
| Product Literature Order No   | 987651-0201                    |
| Product Name                  | ML-XT                          |
| UPC                           | 889056164573                   |
| Physical                      |                                |
| Circuits (maximum)            | 4                              |
| Color - Resin                 | Black                          |
| Gender                        | Receptacle                     |
| Glow-Wire Capable             | No                             |
| Keying to Mating Part         | None                           |
| Lock to Mating Part           | Yes                            |
| Material - Resin              | Nylon                          |
| Net Weight                    | 7.783/g                        |
| Number of Rows                | 2                              |
| Packaging Type                | Bag                            |
| Panel Mount                   | No                             |
| Pitch - Mating Interface      | N/A                            |
| Polarized to Mating Part      | Yes                            |
| Temperature Range - Operating | -55° to +125°C                 |
| Electrical                    |                                |
| Current - Maximum per Contact | 13.0A                          |
| Material Info                 |                                |
| Reference - Drawing Numbers   |                                |
| Application Specification     | 934430010-A                    |
| Packaging Specification       | 934430002-K                    |
| Product Specification         | 934430010-P                    |
| Sales Drawing                 | 934430030-000                  |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - ED/71/2019 (16 July 2019)                 |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

[93444 Series](#)

Mates With

ML-XT Sealed 4 Circuit Plug Housing [934453201](#)

Use With

ML-XT Male (Pin) Terminal [845240004](#) (Nickel), ML-XT Male (Pin) Terminal [845240014](#) (Selective Gold), ML-XT 4 Circuit Receptacle Wedgelock [93447](#) , ML-XT Blind Cavity Plug [934941000](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

|                                  |                           |
|----------------------------------|---------------------------|
| Global                           |                           |
| Description                      | Product #                 |
| Extraction Tool for ML-XT Sealed | <a href="#">638245300</a> |

This document was generated on 11/05/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93444-3201](#)