

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000002](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Threaded Extension Tube, Nickel-plated Brass, Male-to-Female, Pg16-to-Pg16

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Accessory Type	Threaded Extension Tube
Material - Tubing	Nickel-plated Brass
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Accessories
Product Name	GWconnect
UPC	887191812847
Physical	
Net Weight	31.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +200°C
Thread Size	Pg16
Thread Type	(Pg)
Material Info	
Engineering Number	7000.6789.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93600 Series](#)

Use With
HC - High Construction Enclosures, Flexible Conduits, and other Applications as an Extension Tube.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0002](#)