

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000004](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Threaded Extension Tube, Nickel-plated Brass, Male-to-Female, M25-to-M25](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Accessory Type	Threaded Extension Tube
Material - Tubing	Nickel-plated Brass
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Accessories
Product Name	GWconnect
UPC	887191812861

Physical

Net Weight	39.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +200°C
Thread Size	M25
Thread Type	(M) Metric

Material Info

Engineering Number	7000.6791.0
--------------------	-------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93600 Series](#)

Use With

HC - High Construction Enclosures, Flexible Conduits, and other Applications as an Extension Tube.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0004](#)