

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936000048

Status: Active

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect Metal Cable Gland, with Washer and Gaskets, M32x1.5 Thread

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93600</u>
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 16.00, 19.00, 22.00, and 25.00 internal diameters.
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191826202

Physical

Cable Diameter	15.50-24.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	44.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	M32x1.5
Thread Type	(M) Metric

Material Info

Engineering Number	7000.6850.0
--------------------	-------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

93600 Series

Use With

Enclosures Size A and B metal type

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0048](#)