

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000212

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect EMC - Electromagnetic Compatibility, Metal Cable Gland, with Gasket, for 15.00-20.00mm Cable, M32x1.5 Thread

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 - EMC
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	EN 50262
UPC	887191842448
Physical	
Cable Diameter	15.00-20.00mm
Flammability	UL 94V-0
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel
Net Weight	117.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	M32x1.5
Thread Type	(M) Metric
Material Info	
Engineering Number	7000.7336.0



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93600 Series

Use With

Where Electromagnetic Compatibility is required, industrial connectors, hoods, housings, sealed enclosures, and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0212](#)