

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0936000220](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** GWconnect EMC - Electromagnetic Compatibility, Metal Cable Gland, with Gasket, for 13.00-18.00mm Cable, Pg21 Thread

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                                       |
|-------------------------------|-------------------------------------------------------|
| <b>General</b>                |                                                       |
| Product Family                | Industrial Connectors / Enclosures                    |
| Series                        | <a href="#">93600</a>                                 |
| Cable Gland Type              | IP68 - EMC                                            |
| IP Rating                     | IP68                                                  |
| Overview                      | <a href="#">GWconnect Heavy Duty Connectors (HDC)</a> |
| Product Category              | Cable Glands                                          |
| Product Name                  | GWconnect                                             |
| Standard                      | DIN 40430                                             |
| UPC                           | 887191843124                                          |
| <b>Physical</b>               |                                                       |
| Cable Diameter                | 13.00-18.00mm                                         |
| Flammability                  | UL 94V-0                                              |
| Material - Cable Gland        | Brass                                                 |
| Material - Gasket             | Elastomer                                             |
| Material - Plating            | Nickel                                                |
| Net Weight                    | 51.000/g                                              |
| Packaging Type                | Bag                                                   |
| Temperature Range - Operating | -40° to +125°C                                        |
| Thread Size                   | Pg21                                                  |
| Thread Type                   | (Pg)                                                  |
| <b>Material Info</b>          |                                                       |
| Engineering Number            | 7000.7345.0                                           |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Reviewed</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[93600 Series](#)

**Use With**  
Where Electromagnetic Compatibility is required, industrial connectors, hoods, housings, sealed enclosures, and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0220](#)