

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000245

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Stainless Steel Cable Gland with Gasket, for 22.00-32.00mm Cable, Pg36 Thread



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN 40430
UPC	887191844572
Physical	
Cable Diameter	22.00-32.00mm
Flammability	UL 94V-0
Material - Cable Gland	Stainless Steel
Material - Gasket	Elastomer
Net Weight	169.000/g
Packaging Type	Bag
Panel Cutout Diameter	47.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg36
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68
Material Info	
Engineering Number	7000.7400.0

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93600 Series

Use With

Industrial connector, hoods, housings where higher protection and pulling strength are required, for sealed enclosures and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0245](#)