

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000246](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Stainless Steel Cable Gland with Gasket, for 32.00-38.00mm Cable, Pg42 Thread



Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN 40430
UPC	887191844589
Physical	
Cable Diameter	32.00-38.00mm
Flammability	UL 94V-0
Material - Cable Gland	Stainless Steel
Material - Gasket	Elastomer
Packaging Type	Bag
Panel Cutout Diameter	54.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg42
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68
Material Info	
Engineering Number	7000.7401.0

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS Green Image Not Relevant Not Contained

Search Parts in this Series
[93600 Series](#)

Use With
Industrial connector, hoods, housings where higher protection and pulling strength are required, for sealed enclosures and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0246](#)