

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936000371

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect Plastic Gable Gland, with Gasket and Nut, M40x1.5 Thread, Black RAL 9005

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93600</u>
Cable Gland Type	IP68 with Nut and Gasket
IP Rating	IP68
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN EN 50262, EN 60529
UPC	887191853635

Physical

Cable Diameter	22.00-32.00mm
Flammability	UL 94V-2
Gland Color	Black RAL 9005
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	52.000/g
Packaging Type	Bag
Panel Cutout Diameter	40.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	M40x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Material Info

Engineering Number 7000.7826.6



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

93600 Series

Use With

Sealed enclosures and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93600-0371](#)