

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000395

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Plastic Gable Gland, with Gasket and Nut, Pg9 Thread, Black RAL 9005

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 with Nut and Gasket
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN 40430, EN 60529
UPC	887191854977
Physical	
Cable Diameter	4.00-8.00mm
Flammability	UL 94V-2
Gland Color	Black RAL 9005
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	8.000/g
Packaging Type	Bag
Panel Cutout Diameter	15.40mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	Pg9
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68
Material Info	
Engineering Number	7000.7830.6



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93600 Series

Use With

Sealed enclosures and boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93600-0395