

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936010034
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: GWconnect Stamped Crimp Contact for 10A Inserts and Modules, Male, Gold (Au) Plated Phosphor Bronze, 0.75-2.50mm² (18-14 AWG), 400 per Reel



Series image - Reference only

Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA 256883
UL E249674

General

Product Family Industrial Connectors / Enclosures
Series 93601
Contact Type Stamped Crimp Contact
Overview GWconnect® Heavy Duty Connectors (HDC)
Product Category Contacts
Product Name GWconnect
UPC 887191866123

Physical

Gender Male
Material - Contact Phosphor Bronze
Material - Plating Gold
Net Weight 0.400/g
Number of Grooves 0
Packaging Type Reel
Stripping Length 3.20mm
Wire Size AWG 14-18
Wire Size mm² 0.75-2.50

Electrical

Current - Maximum per Contact 10.0A

Material Info

Engineering Number 7100.4078.1

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Mates With

93601 Female Stamped Crimp Contact

Use With

S-D, S-K, S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0034](#)