

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010043](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Turned Crimp Contact for 10A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 0.75mm² (18 AWG), 100 per Bag

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191866710
Physical	
Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	0.700/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	8.00mm
Wire Size AWG	18
Wire Size mm²	0.75
Electrical	
Current - Maximum per Contact	10.0A
Material Info	
Engineering Number	7100.4203.0
Reference - Drawing Numbers	
Sales Drawing	936010039-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Contained Per -ED/88/2018 (15 January 2019) Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series 93601 Series
Mates With 93601 Male Turned Crimp Contact
Use With S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0043](#)