

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010077

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Crimp Contact Insert, Female, 7-Pole, 10A, for Crimp Contacts, Size 3A «21x21», Grey

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		3A «21x21»
Component Type		Inserts - Crimp Contact
Insert Series		SD-7
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC		887191868851
Physical		
Durability (mating cycles max)		500
Flammability		UL 94V-0
Gender		Female
Insert Color		Grey
Material - Insert		Polycarbonate
Net Weight		5.300/g
Number of Rows		3
Packaging Type		Bag
Polarized to Mating Part		Yes
Poles		7
Temperature Range - Operating		-40° to +125°C
Electrical		
Current - Maximum per Contact		10.0A
Voltage - Maximum		250V
Material Info		
Engineering Number		7107.4001.0



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Mates With

936010079 Male Crimp Contact Insert

Use With

Turned or Stamped Contacts - Female

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0077](#)